

## SLIK PRO AL-523BH5AC

**ProdCode: SLI3278**

PRO AL-523BH5AC Tripod with PBH-535AC Ball Head



[\[Download Images\]](#) (.zip file)

### Features

- PRO AL-523BH5AC Tripod with PBH-535AC Ball Head
- Features SLIK original R.F.M. (Rapid Flip Mechanism) - easy way to adjust the leg angle
- Bubble level for easy horizon correction

The SLIK PRO AL-500 series medium-size tripod are capable of handling the weight of professional full-frame DSLRs or mirrorless cameras with heavy lenses.

The PRO AL-523BH5 is a new addition to the best-selling PRO 500BH5. The new series reduce vibration and increase the torsion strength through a re-engineered tripod collar and leg joint.

The new series features SLIK original R.F.M. (Rapid Flip Mechanism) that provides an easy way to adjust the leg angle, a bubble level for easy horizon correction and an accessory hole that will accept your choice of extension arms for mounting monitors, lights tablets, or other photographic accessories.

The PRO AL-523BH5 includes the PBH-523AS ball head with “Cam Lock” Arca Swiss type quick release. This head has an easy-grip ball lock lever. There is a separate panoramic lock on the base, locking the level or angle of the ball but allowing the camera to pan. There are also 360-degree markings around the base for taking photos to stitch together for panoramic shots.

## **Features**

### **Precision Ball Head with Arca-type QR plate**

The BH5 series system package comes with a precision PBH-535AS ball head that has “Cam Lock” Arca-Swiss type quick-release systems for easy mounting the camera. “Cam Lock” quick-release system allows users to attach or detach a camera from the top of the platform and no need to slide in or out the plate from the groove.

### **Completely redesigned tripod body & leg joint**

The series is completely redesigned its tripod body and leg joint, it reduces vibration and increases the torsion strength.

### **Rapid Flip Mechanism (R.F.M.)**

SLIK original Rapid Flip Mechanism (R.F.M.) offers fast and stress-free leg angle adjustments.

---

### **Need Further Support?**

If you have any questions or require additional support regarding this product release, please do not hesitate to contact us. Our team is here to assist you with any inquiries or provide further information or marketing collateral as needed.

### **Contact Us:**

- Marketing - [marketing@holdan.co.uk](mailto:marketing@holdan.co.uk)
- Sales - [sales@holdan.co.uk](mailto:sales@holdan.co.uk)
- Technical Enquiries - [techsales@holdan.co.uk](mailto:techsales@holdan.co.uk)
- Request Demo product loans - [demo@holdan.co.uk](mailto:demo@holdan.co.uk)

We value your partnership and are committed to ensuring a successful product launch. Thank you for your continued support.